

Kroepelin
Längenmesstechnik

Digital internal quick caliper, Measuring range: 10-30 mm



Order data

Order number	438974 10-30
GTIN	2050001055200
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. **Digital display of the absolute value.**

By entering **preset values**, variations can be determined against any value.

Supplied with:

1 battery No. 081561 size LR3, operating instructions.

Optional extras:

Data cable adapter No. 498954 size A2, data cable No. 497440.

Graduations: 0.01 mm

Error limit: 0.03 mm

Repetition accuracy: 0.01 mm

Carbide spherical point \varnothing : 1 mm

minimum groove width: 1.2 mm

maximum groove depth: 5.2 mm

Technical description

minimum groove width	1.2 mm
Carbide spherical point \varnothing	1 mm
maximum contact point length L (measurement depth)	85 mm
Gauging force	1.1 - 1.6 N
Repetition accuracy	0.01 mm

Graduations	0.01 mm
maximum groove depth	5.2 mm
Measuring range	10 - 30 mm
Error limit	0.03 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 LR3
Norm	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	Digimatic interface
IP Index of Protection	IP 67
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Calibration	C7
Type of product	Internal quick calipers

Services

Calibration External / internal quick caliper	013850
Labelling laser-etched Type	018940
DAkkS calibration External / internal quick caliper	011320

Accessories

Receiver / USB keyboard interface Type	498965
Transmitter Type S2	498966 S2
Alkaline-manganese batteries International size LR3	081556 LR3
Interface adapter Type A2	498954 A2
Multi-receiver / USB keyboard interface Type	498975
Connecting cable Type D1	497440 D1
Connecting cable Type D2	497440 D2

Connecting cable Type USB2

497440 USB2