

Kroepelin
Längenmesstechnik

External quick caliper with dial gauge for pipes, Measuring range: 0-50mm



Order data

Order number	438560 0-50
GTIN	2050001036780
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Scale divisions	0.05 mm
Carbide spherical point \varnothing	3 mm
Dial indicator \varnothing	66 mm
maximum contact point length L (measurement depth)	169 mm
Measuring range	0 - 50 mm
minimum bore \varnothing	12 mm
IP Index of Protection	IP 65
Error limit	0.05 mm
Standard	Manufacturer's standard
Measurement technology	analogue
Calibration	C7

Type of product

External quick callipers

Services

Calibration External / internal quick caliper Type S

023450 S

DAkkS calibration External / internal quick caliper Type S

023460 S