



## Feeler gauge shim roll 12.7 mm×5 m, stainless steel, Thickness: 0,05mm



### Order data

Order number	478505 0,05
GTIN	2050001054821
Item class	48B

### Description

#### Version:

Cold rolled, hard spring feeler strip steel of maximum precision. From size 0.02, the strip thickness is continuously marked and cannot be wiped off (exception: for No. 478502 from size 0.08).

Stored in a practical dispenser; pull out like a tape measure. The desired length can be cut from the 5 or 10 m long strip.

**Non-rusting** acid-resistant stainless steel, material No. 1.4310 (or 1.4301 for thickness 0.005–0.05 mm), cold rolled, spring hardened, bright surface.

#### Application:

In jig and tool building for aligning and adjusting machine parts, as a shim for aligning components, for tolerance measurements of all kinds, for checking fits and guides, for setting up printing rollers.

### Technical description

Thickness	0.05 mm
Error limit	±3 µm
Standard	Works standard

Tolerance	T3
Material	stainless steel
Material	Stainless steel, INOX
Roll length	5 m
Roll width	12.7 mm
Type of product	Feeler gauge shim strip