



## Shim stock 150×2500 mm, non-alloy steel, Thickness: 0,025mm



### Order data

Order number	478700 0,025
GTIN	4045197207784
Item class	42H

### Description

#### Version:

This precision gauging shim is provided on rolls in plastic boxes (easy to pull off). The individual boxes can be stacked in a block, saving space and protecting the material from dirt.

**C-steel** – Carbon steel, material No. 1.0330 (DC01 C490 MA), cold rolled, bright surface.

#### Application:

**Setting** tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

### Technical description

Thickness	0.025 mm
Material	Carbon steel
Error limit	±2 µm
Film length	2500 mm
Film width	150 mm
Product name attribute	non-alloy steel
Type of product	Shim stock

