

**Kroepelin**  
Längenmesstechnik

## Digital internal quick caliper with long contact points, Measuring range: 70-100 mm



### Order data

Order number	438978 70-100
GTIN	2050001743190
Item class	46Q

### Description

#### Version:

1 fixed and 1 movable arm with carbide spherical contact points. **Digital display of the absolute value.**

By entering **preset values**, variations can be determined against any value.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Supplied with 2 batteries No. 081561 size LR3, operating instructions.

#### Optional extras:

Data cable adapter No. 498954 size A2; data cable No. 497440; radio adapter No. 498954 size A5.

IP Index of Protection: IP 67

Graduations can be switched over: 0.001 mm

Graduations can be switched over: 0.002 mm

Graduations can be switched over: 0.05 mm

Graduations can be switched over: 0.01 mm

Graduations can be switched over: 0.02 mm

Graduations can be switched over: 0.005 mm

### Technical description

Repetition accuracy	0.02 mm
---------------------	---------

Measuring range	70 - 100 mm
maximum contact point length L (measurement depth)	127 mm
Carbide spherical point $\varnothing$	2 mm
Gauging force	1.3 - 1.8 N
minimum groove width	2.5 mm
maximum groove depth	8.5 mm
Error limit	0.04 mm
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	2
IP Index of Protection	IP 67
Power supply	Battery-powered
Graduations can be switched over	0.001 mm
Graduations can be switched over	0.002 mm
Graduations can be switched over	0.05 mm
Graduations can be switched over	0.01 mm
Graduations can be switched over	0.02 mm
Graduations can be switched over	0.005 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Bluetooth interface
Interface	USB interface
Interface	USB interface
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Calibration	C7
Type of product	Internal quick calipers

## Services

Calibration External / internal quick caliper	013850
---	--------

Labelling laser-etched Type	018940
DAkkS calibration External / internal quick caliper	011320

### Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
Connecting cable Type D1	497440 D1
Interface adapter Type A2	498954 A2
Connecting cable Type USB2	497440 USB2
Connecting cable Type D2	497440 D2
Transmitter Type S2	498966 S2
Receiver / USB keyboard interface Type	498965
Multi-receiver / USB keyboard interface Type	498975
Alkaline-manganese batteries International size LR3	081561 LR3