

HOLEX**Feeler gauge shim roll 12.7 mm×10 m, Carbon steel, Thickness: 0,07mm****Order data**

| | |
|--------------|---------------|
| Order number | 478504 0,07 |
| GTIN | 4045197524140 |
| Item class | 42H |

Description**Version:**

Cold rolled, hard spring feeler strip steel of maximum precision. From size 0.02, the strip thickness is continuously marked and cannot be wiped off (exception: for No. 478502 from size 0.08).

Stored in a practical dispenser; pull out like a tape measure. The desired length can be cut from the 5 or 10 m long strip.

C-steel – Carbon steel, material No. 1.1274, cold rolled, hardened, bright surface. **(size 0.01 and 0.02 stainless).**

Application:

In jig and tool building for aligning and adjusting machine parts, as a shim for aligning components, for tolerance measurements of all kinds, for checking fits and guides, for setting up printing rollers.

Technical description

| | |
|-------------|---------|
| Thickness | 0.07 mm |
| Error limit | ±4 µm |

| | |
|-----------------|-------------------------|
| Standard | Works standard |
| Tolerance | T3 |
| Material | Carbon steel |
| Roll length | 10 m |
| Roll width | 12.7 mm |
| Type of product | Feeler gauge shim strip |