

Kroepelin
Längenmesstechnik**Internal quick caliper with long contact points, Measuring range: 70-120mm****Order data**

Order number	438953 70-120
GTIN	2050001743152
Item class	46Q

Description**Version:**

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

maximum contact point length L (measurement depth)	192 mm
Scale divisions	0.05 mm
Carbide spherical point \varnothing	2 mm
minimum groove width	3.3 mm
maximum groove depth	8 mm
Measuring range	70 - 120 mm
Error limit	0.05 mm
Dial indicator \varnothing	66 mm
Calibration	C7
IP Index of Protection	IP 65

Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Internal quick caliper

Services

DAkkS calibrationExternal / internal quick caliper Type S	023460 S
CalibrationExternal / internal quick caliper Type S	023450 S