

**Forked clamp with shoe, DIN 6315 GN, Slot width×overall length: 26X315mm****Order data**

Order number	371400 26X315
GTIN	4020772070953
Item class	35A

**Description****Material:**

Quenched and tempered steel, painted.

**Technical description**

Slot width	26 mm
overall length	315 mm
for clamping screws	M24
Height	40 mm
Width	70 mm
Type	6315GN
Standard	DIN 6315 GN
Type of product	Plain clamp