

**Forked clamp offset, Slot width a: 12mm****Order data**

Order number	370810 12
GTIN	4020772073190
Item class	35A

Description**Version:**

Quenched and tempered steel, painted.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Material:

Screw strength 8.8.

Supplied with:

Adjusting screw and T-bolts DIN 787 (see No. 375300).

Technical description

Tee bolt DIN 787, No. 375300	Size 1212100
Distance e from tip to end of slot	90 mm
Slot width a	12 mm
Clamping height h	10 - 48 mm
Length L	125 mm

Height H	25 mm
Width B	40 mm
Type	6315V
Type of product	Plain clamp

Accessories

Detent clamp lever Slot width a 12 mm	370750 12
---------------------------------------	-----------