

**Forked clamp with shoe, DIN 6315 GN, Slot width×overall length: 11X125mm****Order data**

Order number	371400 11X125
GTIN	4020772070878
Item class	35A

Description**Material:**

Quenched and tempered steel, painted.

Technical description

Slot width	11 mm
Height	20 mm
Width	30 mm
overall length	125 mm
for clamping screws	M10
Type	6315GN
Standard	DIN 6315 GN
Type of product	Plain clamp