



Forked clamp offset, Slot width a: 16mm



Order data

Order number	370810 16
GTIN	4020772073244
Item class	35A

Description

Version:

Quenched and tempered steel, painted.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Material:

Screw strength 8.8.

Supplied with:

Adjusting screw and T-bolts DIN 787 (see No. 375300).

Technical description

Tee bolt DIN 787, No. 375300	Size 1616125
Distance e from tip to end of slot	110 mm
Slot width a	16 mm
Clamping height h	13 - 58 mm
Length L	160 mm

Height H	30 mm
Width B	50 mm
Type	6315V
Type of product	Plain clamp

Accessories

Detent clamp lever Slot width a 16 mm	370750 16
---------------------------------------	-----------