



Clamp, light design, Slot×length of clamping screw: 20X200 mm



Order data

Order number	370830 20X200
GTIN	4020772377564
Item class	35A

Description

Advantage:

Thanks to the enormous saving in weight by lightweight design, this clamp can also be used for other clamping applications, even on rotating assemblies. No further clamp blocks are needed to achieve the required clamping height.

Supplied with:

Complete with clamping screw DIN 787.

Note:

The adjustment screw No. 370840 must be ordered separately.

Clamping height h: 16 - 89.5 mm

Tee bolt DIN 787, No. 375300: Size 2020200

Length L: 200 mm

Width B: 49 mm

Height H: 44 mm

Thread G: M20

Technical description

Tee bolt DIN 787, No. 375300	Size 2020200
Clamping screw length	200 mm

Thread G	M20
Slot width a	20 mm
Clamping height h	16 - 89.5 mm
Length L	200 mm
Width B	49 mm
Height H	44 mm
Type	6311
Type of product	Plain clamp

Accessories

Support screw Thread G × Length L 16X55	370840 16X55
Support screw Thread G × Length L 16X90	370840 16X90
Support screw Thread G × Length L 20X109	370840 20X109
Support screw Thread G × Length L 24X137	370840 24X137
Support screw Thread G × Length L 12X49	370840 12X49
Support screw Thread G × Length L 12X94	370840 12X94
Support screw Thread G × Length L 10X39	370840 10X39
Support screw Thread G × Length L 20X69	370840 20X69
Support screw Thread G × Length L 30X180	370840 30X180
Support screw Thread G × Length L 24X87	370840 24X87