

**Forked clamp with shoe, DIN 6315 GN, Slot width×overall length: 14X200mm****Order data**

Order number	371400 14X200
GTIN	4020772070892
Item class	35A

Description**Material:**

Quenched and tempered steel, painted.

Technical description

for clamping screws	M12; M14
Height	25 mm
Width	40 mm
overall length	200 mm
Slot width	14 mm
Type	6315GN
Standard	DIN 6315 GN
Type of product	Plain clamp