

**Forked clamp offset, Slot width a: 20mm****Order data**

Order number	370810 20
GTIN	4020772073268
Item class	35A

Description**Version:**

Quenched and tempered steel, painted.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Material:

Screw strength 8.8.

Supplied with:

Adjusting screw and T-bolts DIN 787 (see No. 375300).

Technical description

Tee bolt DIN 787, No. 375300	Size 2020160
Slot width a	20 mm
Distance e from tip to end of slot	135 mm
Clamping height h	16 - 77 mm
Length L	200 mm

Height H	40 mm
Width B	60 mm
Type	6315V
Type of product	Plain clamp