

**Forked clamp offset, Slot width a: 22mm****Order data**

Order number	370810 22
GTIN	4020772073282
Item class	35A

Description**Version:**

Quenched and tempered steel, painted.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Material:

Screw strength 8.8.

Supplied with:

Adjusting screw and T-bolts DIN 787 (see No. 375300).

Technical description

Distance e from tip to end of slot	135 mm
Slot width a	22 mm
Tee bolt DIN 787, No. 375300	Size 2220160
Clamping height h	16 - 75 mm
Length L	200 mm

Height H	40 mm
Width B	60 mm
Type	6315V
Type of product	Plain clamp