



## Clamp with plastic cap, Slot width a: 10 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 370820 10     |
| GTIN         | 4020772100285 |
| Item class   | 35A           |

### Description

#### Version:

Clamp with plastic cap and captive contact piece.

#### Advantage:

Saving in weight by lightweight design, variable and quick adjustment at a distance from the workpiece. No further clamp blocks are needed to achieve the required clamping height. The plain washer is captive on the clamp.

#### Supplied with:

Complete with clamping screw DIN 787.

Clamping height h: 0 - 15 mm

Tee bolt DIN 787, No. 375300: Size 101080

Length L: 80 mm

Width B: 44 mm

Height H: 32 mm

### Technical description

|                              |             |
|------------------------------|-------------|
| Slot width a                 | 10 mm       |
| Tee bolt DIN 787, No. 375300 | Size 101080 |
| Clamping height h            | 0 - 15 mm   |

|                 |             |
|-----------------|-------------|
| Length L        | 80 mm       |
| Height H        | 32 mm       |
| Width B         | 44 mm       |
| Type            | 6310        |
| Type of product | Plain clamp |