

**Forked clamp with shoe, DIN 6315 GN, Slot width×overall length: 22X315mm****Order data**

Order number	371400 22X315
GTIN	4020772070939
Item class	35A

Description**Material:**

Quenched and tempered steel, painted.

Technical description

Slot width	22 mm
Width	60 mm
for clamping screws	M20; M22
overall length	315 mm
Height	40 mm
Type	6315GN
Standard	DIN 6315 GN
Type of product	Plain clamp