



Magnetic measuring stand with fine adjustment at the column, Type: 290



Order data

Order number	441150 290
GTIN	7290005395017
Item class	46G

Description

Version:

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Universal indicator holder with fine adjustment, for clamping shank \varnothing 8 mm, \varnothing 6 mm, \varnothing 3/8 inch and indicators with dovetail clamping shanks.

Callout:

Fine adjustment at the indicator holder

Technical description

Magnetic base length	60 mm
Magnetic base width	50 mm
Throat	317 mm
Magnetic force	800 N
maximum loading	8 kg

Length of jointed arm L ₂	113 mm
Magnetic base height	55 mm
Length of jointed arm L ₁	133 mm
Connection thread at bottom	M8
Type of product	measuring stand

Accessories

Holder for measuring stand Type 2SM	442104 2SM
Stand base Type V	442120 V
Holder for measuring stand Type K2	442100 K2
Stand base Type 0	442140 0
Holder for measuring stand Type 2SM	442100 2SM
Stand base Type 0	442120 0
Holder for measuring stand Type H	442100 H
Stand base Type 1	442120 1
Stand base Type K3	442120 K3
3-D jointed arm Type 290	442110 290
Stand base Type 1	442140 1
Holder for measuring stand Type CA	442100 CA
Stand base Type 1	440868 1
Stand base with fine adjustment Type 0	442125 0
Holder for measuring stand Type QR	442100 QR
Holder for measuring stand Type K1	442100 K1
3-D jointed arm Type 290	442114 290