



## Digital universal caliper DIGI ULISSE I/E, Measuring range: 250mm



### Order data

Order number	417700 250
GTIN	2050001670816
Item class	46P

### Description

**Version:**

Digital universal caliper for a variety of internal and external measurements, with exchangeable measuring tips.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Digital caliper including 1 battery No. 081560 size CR2032. Interchangeable measuring tips with ball  $\varnothing$  2.5 mm.

**Optional extras:**

For size 400 - 650 all replacement and special contact points No. 434900 - 4910 with M2.5 thread can be used, data cable No. 498948.

**Note:**

Other measuring tips on request.

### Technical description

Measuring range outside	0 - 210 mm
Measuring range	0 - 250 mm
Measuring range inside	24 - 250 mm
Ball $\varnothing$ measuring tips	2.5 mm
IP Index of Protection	IP 67
Jaw length	64 mm

Calibration	A1
Scale divisions	0.01 mm
Error limit	0.03 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	RS232 interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300

## Accessories

Connection cable Duplex Type 2	498950 2
Accessories for calipers Type TAST	417701 TAST
Connection cable Type R2	498948 R2
Button cell / special battery Battery type CR2032	081560 CR2032
Connection cable Type USB2	498948 USB2
Accessories for calipers Type BUCHSE	417701 BUCHSE

Connection cable Duplex Type USB2

498950 USB2