



3-D jointed arm, Type: 120



Order data

Order number	442114 120
GTIN	4045197551214
Item class	42D

Description

Version:

Mechanical 3-D jointed arm with central locking. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning.

Length of jointed arm L_1 : 56 mm

Length of jointed arm L_2 : 51 mm

External thread \varnothing bottom: M5

Internal thread \varnothing top: M6

Technical description

Length of jointed arm L_2	51 mm
External thread \varnothing bottom	M5
Length of jointed arm L_1	56 mm
Internal thread \varnothing top	M6
Type of product	measuring stand

Accessories

Holder for measuring stand Type K1	442100 K1
Holder for measuring stand Type H	442100 H
Stand base Type S	442140 S
Holder for measuring stand Type K2	442100 K2
Holder for measuring stand Type QR	442100 QR
Holder for measuring stand Type CA	442100 CA
Holder for measuring stand Type 2SM	442104 2SM
Holder for measuring stand Type 2SM	442100 2SM
Stand base Type S	442120 S