



## Digital workshop caliper, Measuring range: 1500 mm



### Order data

Order number	415530 1500
GTIN	4045197348531
Item class	42A

### Description

#### Version:

Easy-to-read display. Optimum guidance and sliding characteristics due to **double Vee guides**. Stainless steel jaws, precision ground. The left-hand measurement jaw is moveable. With Sylvac electronics.

#### Supplied with:

Manufacturer's test certificate. Up to size 1000 including plastic wallet, from size 1500 sturdy transport packaging.

1 battery No. 081560 size CR2032

Packaging: sturdy box

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.1 mm

Jaw length: 150 mm

Internal jaw  $\varnothing$ : 20 mm

Weight: 2 kg

### Technical description

Jaw length	150 mm
Measuring range	0 - 1500 mm
Calibration	A1
Internal jaw $\varnothing$	20 mm
Weight	2 kg
Scale divisions	0.01 mm

Error limit	0.1 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

### Services

Calibration Calipers / depth gauges maximum measuring range 2000 mm	011030 2000
Labelling laser-etched Type	018940
Calibration Calipers / depth gauges maximum measuring range 2000 mm	021000 2000

### Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------