



Length tape measure CJL-INOX, Band length: 4800mm



Order data

Order number	415198 4800
GTIN	2050001677082
Item class	46P

Description

Version:

Length tape measure CJL-INOX for measuring plane parallel distances. Graduations 1 mm. Precise, high contrast laser graduations. Reading 0.1 mm. Graduation error limits to DIN 866.

Note:

For measuring tape for measuring diameter and circumference, see No. 465680; 465682.

Technical description

Band length	4800 mm
Tape width	16 mm
Measuring range	3400 - 4800 mm
Standard	DIN 866
Scale divisions	0.1 mm
Material	Stainless steel, INOX
Calibration	G2
Type of product	Measuring tape

Services

026280 6000

CalibrationCircumference tape measure maximum length
6000 mm

