



TWIN CAL digital workshop caliper IP67 with measuring tips, Measuring range: 1000mm



Order data

Order number	415357 1000
GTIN	7630041106473
Item class	45A

Description

Version:

Large digital display 11 mm, "Soft touch" casing, automatic shut-down (2h), TLC- TWIN interface for data transmission. Operation time: approx. 12000 hours.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

Technical description

Internal jaw \varnothing	20 mm
Jaw length	150 mm
Measuring range	0 - 1000 mm
Calibration	A1
Reversible reading	mm / inch
Scale divisions	0.0005 in
Scale divisions	0.01 mm

Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.05 mm
Standard	ISO 13385
Interface	Digimatic interface
Interface	USB interface
Interface	TESA Link Connector TLC
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 1000 mm	021010 1000
Calibration Calipers / depth gauges maximum measuring range 1000 mm	021000 1000

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Data cable TLC, 2 m Type USB	498918 USB