



3-D jointed arm, Type: 240



Order data

Order number	442114 240
GTIN	4045197551221
Item class	42D

Description

Version:

Mechanical 3-D jointed arm with central locking. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning.

Length of jointed arm L₁: 110 mm

Length of jointed arm L₂: 101 mm

External thread Ø bottom: M8

Internal thread Ø top: M6

Technical description

Internal thread Ø top	M6
Length of jointed arm L ₂	101 mm
Length of jointed arm L ₁	110 mm
External thread Ø bottom	M8
Type of product	measuring stand

Accessories

Holder for measuring stand Type H	442100 H
Stand base Type 0	442120 0
Stand base Type K3	442120 K3
Holder for measuring stand Type 2SM	442100 2SM
Holder for measuring stand Type K2	442100 K2
Stand base Type 1	442140 1
Stand base Type V	442120 V
Stand base Type 0	442140 0
Stand base Type 1	442120 1
Holder for measuring stand Type CA	442100 CA
Holder for measuring stand Type QR	442100 QR
Holder for measuring stand Type 2SM	442104 2SM
Holder for measuring stand Type K1	442100 K1