

Mitutoyo**Carbon digital caliper, Measuring range: 2000mm****Order data**

Order number	415400 2000
GTIN	2050001058010
Item class	44A

Description**Version:**

Measured result is displayed in easy-to-read digits.

With drive slide for constant measuring force. Extremely light. Selectable set-point (preset), selection of internal / external measurements (offset).

Function:

IP66: Protected against strong jets of water, and against temporary flooding and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497085.

Technical description

Jaw length	150 mm
Calibration	A1
Weight	2.56 kg
Internal jaw \varnothing	20 mm
Measuring range	0 - 2000 mm
Scale divisions	0.01 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1

Battery type	SR44
IP Index of Protection	IP 66
Power supply	Battery-powered
Measurement deviation E MPE	± 0.12 mm
Standard	ISO 13385
Interface	USB interface
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Packaging	sturdy box
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 2000 mm	021000 2000
---	-------------

Accessories

Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type USB2	497085 USB2
Transmitter Type S11E	498966 S11E
Connecting cable with data switch Type D1	497085 D1
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type 357	081560 357
Connecting cable with data switch Type D2	497085 D2