



3-D jointed arm, Type: 290



Order data

Order number	442114 290
GTIN	4045197551238
Item class	42D

Description

Version:

Mechanical 3-D jointed arm with central locking. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning.

Length of jointed arm L_1 : 149 mm

Length of jointed arm L_2 : 129 mm

External thread \varnothing bottom: M8

Internal thread \varnothing top: M6

Technical description

External thread \varnothing bottom	M8
Internal thread \varnothing top	M6
Length of jointed arm L_1	149 mm
Length of jointed arm L_2	129 mm
Type of product	measuring stand

Accessories

Holder for measuring stand Type K1	442100 K1
Stand base Type 0	442140 0
Stand base Type 1	442120 1
Holder for measuring stand Type K2	442100 K2
Stand base Type V	442120 V
Holder for measuring stand Type QR	442100 QR
Stand base Type 0	442120 0
Holder for measuring stand Type 2SM	442100 2SM
Holder for measuring stand Type 2SM	442104 2SM
Holder for measuring stand Type CA	442100 CA
Stand base Type K3	442120 K3
Holder for measuring stand Type H	442100 H
Stand base Type 1	442140 1