

HOLEX®
Digital workshop caliper, Measuring range: 3000 mm

Order data

Order number	415530 3000
GTIN	4045197348562
Item class	42A

Description
Version:

Easy-to-read display. Optimum guidance and sliding characteristics due to **double Vee guides**.
Stainless steel jaws, precision ground. The left-hand measurement jaw is moveable.
With Sylvac electronics.

Supplied with:

Manufacturer's test certificate. Up to size 1000 including plastic wallet, from size 1500 sturdy transport packaging.

1 battery No. 081560 size CR2032

Packaging: sturdy box

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.25 mm

Jaw length: 150 mm

Internal jaw \varnothing : 20 mm

Weight: 3.4 kg

Technical description

Internal jaw \varnothing	20 mm
Weight	3.4 kg
Calibration	A1
Jaw length	150 mm
Measuring range	0 - 3000 mm
Scale divisions	0.01 mm

Error limit	0.25 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

Labelling laser-etched Type	018940
Calibration Calipers / depth gauges maximum measuring range 3000 mm	011030 3000

Accessories

Button cell / special battery International size CR2032	081560 CR2032
---	---------------