

Mitutoyo**Digital workshop caliper with measuring tips, Measuring range: 1000mm****Order data**

Order number	415350 1000
GTIN	4946368124872
Item class	44A

Description**Version:**

Measured result is displayed in easy-to-read digits.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cables No. 497080 and 497100.

Technical description

Jaw length	150 mm
Measuring range	0 - 1000 mm
Calibration	A1
Internal jaw \varnothing	20 mm
Scale divisions	0.01 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	± 0.07 mm
Standard	ISO 13385
Interface	Digimatic interface

Interface	USB interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibration Calipers / depth gauges maximum measuring range 1000 mm	021010 1000

Accessories

Connecting cable with data switch Type D2	497100 D2
Connecting cable Type D2	497080 D2
Connecting cable Type USB2	497080 USB2
Button cell / special battery Battery type 357	081560 357
Connecting cable Type D1	497080 D1
Connecting cable with data switch Type USB2	497100 USB2
Connecting cable with data switch Type D1	497100 D1