



## Lightweight digital workshop caliper, Measuring range: 300 mm



### Order data

Order number	415510 300
GTIN	2050001060211
Item class	43A

### Description

#### Version:

**Digital workshop caliper in lightweight design** Large digital display. With measuring tips and Vee guides.

Jaws and tips stainless, hardened and ground. Easy precise running on Vee guides. Aluminium beam and slide. 50 % weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic). With RS 232 data output.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Data cable No. 498950 (only for size 300).

Standard: Manufacturer's standard

Reversible reading: mm / inch

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 inch

Error limit: 0.04 mm

Jaw length: 90 mm

Internal jaw  $\varnothing$ : 10 mm

Weight: 0.5 kg

### Technical description

Measuring range	0 - 300 mm
Weight	0.5 kg

Internal jaw Ø	10 mm
Jaw length	90 mm
Reversible reading	mm / inch
Calibration	A1
Scale divisions	0.0005 inch
Scale divisions	0.01 mm
Error limit	0.04 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
Type of product	Workshop calipers

## Services

Calibration Calipers / depth gauges maximum measuring range 300 mm	011030 300
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	011050 300

## Accessories

Receiver / USB keyboard interface Type	498965
Connection cable Duplex Type USB2	498950 USB2
Connection cable Duplex Type 2	498950 2
Button cell / special battery Battery type CR2032	081560 CR2032
Multi-receiver / USB keyboard interface Type	498975
Transmitter Type S6	498966 S6