



TWIN CAL digital workshop caliper IP67 without measuring tips, Measuring range: 300mm



Order data

| | |
|--------------|---------------|
| Order number | 415358 300 |
| GTIN | 7630041106350 |
| Item class | 45A |

Description

Version:

Large digital display 11 mm, "Soft touch" casing, automatic shut-down (2h), TLC- TWIN interface for data transmission. Operation time: approx. 12000 hours.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

Technical description

| | |
|---|---------------|
| Calibration | A1 |
| Reversible reading | mm / inch |
| Internal jaw \varnothing | 10 mm |
| Measuring range | 0 - 300 mm |
| Jaw length | 80 mm |
| Scale divisions | 0.0005 in |
| Scale divisions | 0.01 mm |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |

| | |
|-------------------------------|---------------------------------------|
| Number of batteries contained | 1 |
| IP Index of Protection | IP 67 |
| Power supply | Battery-powered |
| Measurement deviation E MPE | ± 0.04 mm |
| Standard | ISO 13385 |
| Interface | Digimatic interface |
| Interface | USB interface |
| Interface | TESA Link Connector TLC |
| Measured value saving | Once-off setting of the zero position |
| Measurement technology | digital |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Packaging | sturdy box |
| Type of product | Workshop calipers |

Services

| | |
|---|------------|
| CalibrationCalipers / depth gauges maximum measuring range 300 mm | 021000 300 |
| DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm | 021010 300 |

Accessories

| | |
|---|---------------|
| Data cable TLC, 2 m Type USB | 498918 USB |
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |