



## Digital universal caliper DIGI ULISSE I/E, Measuring range: 650mm



### Order data

Order number	417700 650
GTIN	2050001670847
Item class	46P

### Description

**Version:**

Digital universal caliper for a variety of internal and external measurements, with exchangeable measuring tips. RS232C data output.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Digital caliper including 1 battery No. 081560 size CR2032. Interchangeable measuring tips with ball  $\varnothing$  3 mm and clamping sleeve with M2.5 internal thread.

**Optional extras:**

For size 400 - 650 all replacement and special contact points No. 434900 - 4910 with M2.5 thread can be used, data cable No. 498948.

**Note:**

Other measuring tips on request.

### Technical description

Calibration	A1
Measuring range outside	0 - 570 mm
IP Index of Protection	IP 67
Ball $\varnothing$ measuring tips	3 mm
Measuring range	0 - 650 mm
Jaw length	103 mm

Measuring range inside	42 - 650 mm
Scale divisions	0.01 mm
Error limit	0.04 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	RS232 interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

DAkKS calibration Calipers / depth gauges maximum measuring range 1000 mm	021010 1000
Calibration Calipers / depth gauges maximum measuring range 1000 mm	021000 1000

## Accessories

Connection cable Duplex Type USB2	498950 USB2
Steel contact point Type 14	434900 14
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 18/6	434900 18/6
Accessories for calipers Type TAST	417701 TAST

Steel contact point Type 14/40	434900 14/40
Steel contact point Type 14/15	434900 14/15
Steel contact point Type 14/30	434900 14/30
Steel contact point Type 2	434900 2
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 16	434900 16
Steel contact point Type 29/20	434900 29/20
Steel contact point Type 13	434900 13
Connection cable Type R2	498948 R2
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 15	434900 15
Steel contact point Type 20	434900 20
Steel contact point Type 28	434900 28
Carbide contact point Type 18/3	434910 18/3
Button cell / special battery Battery type CR2032	081560 CR2032
Accessories for calipers Type BUCHSE	417701 BUCHSE
Steel contact point Type 11/25	434900 11/25
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 11/20	434900 11/20
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 39	434900 39
Steel contact point Type 18/4	434900 18/4
Steel contact point Type 11	434900 11
Steel contact point Type 11/15	434900 11/15
Steel contact point Type 18/3	434900 18/3
Connection cable Duplex Type 2	498950 2
Steel contact point Type 24	434900 24
Steel contact point Type 10	434900 10

Connection cable Type USB2	498948 USB2
Steel contact point Type 12	434900 12
Steel contact point Type 29/10	434900 29/10
Steel contact point Type 17	434900 17