

 Mahr

## Digital caliper MarCal with measuring tips, Measuring range: 500mm



### Order data

Order number	415320 500
GTIN	4059192002923
Item class	43A

### Description

#### Version:

**Direct reading from large and clear digital display. Precision lapped measuring faces.** The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Data cable No. 498940.

### Technical description

Internal jaw $\varnothing$	20 mm
Jaw length	150 mm
Measuring range	0 - 500 mm
Calibration	A1
Reversible reading	mm / inch
Scale divisions	0.0005 in
Scale divisions	0.01 mm

Error limit	0.04 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Works standard
Interface	USB interface
Interface	Digimatic interface
Interface	RS232 interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

## Services

DAkKS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500
CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500

## Accessories

Connection cablesimplex with data key Type D2	498940 D2
Connection cablesimplex with data key Type USB2	498940 USB2
Button cell / special battery Battery type CR2032	081560 CR2032
Connection cablesimplex with data key Type R2	498940 R2