

Mitutoyo**Digital caliper IP67 with measuring tips, Measuring range: 200 mm****Order data**

Order number	415354 200
GTIN	4946368727103
Item class	44A

Description**Version:**

Measured result is displayed in easy-to-read digits.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497085.

IP Index of Protection: IP 67

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.04 mm

Jaw length: 60 mm

Internal jaw \varnothing : 10 mm

Technical description

Jaw length	60 mm
Calibration	A1
Measuring range	0 - 200 mm
Internal jaw \varnothing	10 mm
Scale divisions	0.01 mm

Error limit	0.04 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200

Accessories

Connecting cable with data switch Type D1	497085 D1
Connecting cable with data switch Type D2	497085 D2
Connecting cable with data switch Type USB2	497085 USB2
Button cell / special battery Battery type 357	081560 357