

## Universal measuring stand



### Order data

Order number	442000
GTIN	4045197204479
Item class	46Q

### Description

#### Version:

All-round machined base with ground contact faces. Vee underside for placing on shafts and cylindrical bodies. Top side with a T-slot for moving the measuring column. Sturdy column. Cross arm with fine adjustment on indicator arm.

#### Application:

For concentricity checks on machine tools and appliances or for parallel measurements on guide slides.

Cross arm  $\varnothing D_1$ : 16 mm

Cross arm length  $L_1$ : 180 mm

Column  $\varnothing D_2$ : 16 mm

Column height  $L_2$ : 300 mm

Stand base length: 250 mm

Stand base width: 60 mm

### Technical description

Column height $L_2$	300 mm
Stand base length	250 mm

Stand base width	60 mm
Cross arm length $L_1$	180 mm
Cross arm $\varnothing D_1$	16 mm
Column $\varnothing D_2$	16 mm
Type of product	measuring stand

---

## Accessories

Fine adjustment complete for dial indicator stand $\varnothing$ dial indicator holder 10 mm	440760 10
Fine adjustment complete for dial indicator stand $\varnothing$ dial indicator holder 8 mm	440760 8