



Lightweight digital workshop caliper, Measuring range: 500mm



Order data

Order number	415510 500
GTIN	2050001060228
Item class	43A

Description

Version:

Digital workshop caliper in lightweight design Large digital display. With measuring tips and Vee guides.

Jaws and tips stainless, hardened and ground. Easy precise running on Vee guides. Aluminium beam and slide. 50 % weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

Supplied with:

1 battery No. 081560 size CR2032

Technical description

Measuring range	0 - 500 mm
Reversible reading	mm / inch
Internal jaw \varnothing	20 mm
Jaw length	150 mm
Calibration	A1
Weight	1.4 kg
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Error limit	0.05 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032

Number of batteries contained	1
Power supply	Battery-powered
Standard	Works standard
Measurement technology	digital
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500
CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------