

**Mitutoyo**
**Digital caliper IP67 with measuring tips, Measuring range: 300 mm**

**Order data**

Order number	415354 300
GTIN	4946368585352
Item class	44A

**Description**
**Version:**

Measured result is displayed in easy-to-read digits.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497085.

IP Index of Protection: IP 67

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.05 mm

Jaw length: 90 mm

Internal jaw  $\varnothing$ : 10 mm

**Technical description**

Measuring range	0 - 300 mm
Calibration	A1
Internal jaw $\varnothing$	10 mm
Jaw length	90 mm
Scale divisions	0.01 mm

Error limit	0.05 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

## Services

Calibration Calipers / depth gauges maximum measuring range 300 mm	011030 300
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	011050 300

## Accessories

Button cell / special battery Battery type 357	081560 357
Connecting cable with data switch Type USB2	497085 USB2
Connecting cable with data switch Type D1	497085 D1
Connecting cable with data switch Type D2	497085 D2