



Slitting saw arbor, for saw blade \varnothing d₁: 100mm



Order data

Order number	345510 100
GTIN	4045197698902
Item class	32X

Description

Version:

Precisely tempered, ground on the external and internal \varnothing , shank to DIN 1835 B. Concentricity 0.01 mm. **For side lock arbor with bore \varnothing (d₃) 20 or 25 mm.**

Application:

For holding slitting saws No. 175000 – 179820 with \varnothing (d₁) from 20 – 100 mm and saw blade thicknesses from 0.2 – 6 mm.

Supplied with:

Arbor, clamping screw and intermediate ring.

Technical description

\varnothing d ₂	22 mm
\varnothing d ₄	39.5 mm
\varnothing d ₃	25 mm
Length L	150 mm
for saw blade \varnothing d ₁	100 mm
A	92 mm
Type of product	Slitting saw arbor

Accessories

Spare screw for slitting saw arbor for saw blade \varnothing d1 100 mm

345566 100

Spare washer for slitting saw arbor for saw blade \varnothing d1 100 mm

345561 100