

 Mahr**Lightweight digital workshop caliper, Measuring range: 800mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 415510 800    |
| GTIN         | 2050001060235 |
| Item class   | 43A           |

**Description****Version:**

**Digital workshop caliper in lightweight design** Large digital display. With measuring tips and Vee guides.

Jaws and tips stainless, hardened and ground. Easy precise running on Vee guides. Aluminium beam and slide. 50 % weight advantage. Wear and scratch resistant with hard anodised surface 1100 HV (similar to ceramic).

**Supplied with:**

1 battery No. 081560 size CR2032

**Technical description**

|   |               |
|---|---------------|
| Jaw length  | 150 mm        |
| Calibration   | A1            |
| Weight  | 1.6 kg        |
| Measuring range   | 0 - 800 mm    |
| Internal jaw $\varnothing$                              | 20 mm         |
| Reversible reading                                      | mm / inch     |
| Scale divisions   | 0.0005 in     |
| Scale divisions   | 0.01 mm       |
| Error limit   | 0.07 mm       |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |

|                               |                   |
|-------------------------------|-------------------|
| Number of batteries contained | 1                 |
| Power supply                  | Battery-powered   |
| Standard                      | Works standard    |
| Measurement technology        | digital           |
| Type of product               | Workshop calipers |

## Services

|  |             |
|--|-------------|
| DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm | 021010 1000 |
| CalibrationCalipers / depth gauges maximum measuring range 1000 mm       | 021000 1000 |

## Accessories

|   |               |
|---|---------------|
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |
|---|---------------|