

**Slitting saw arbor, for saw blade Ø d₁: 25mm****Order data**

Order number	345510 25
GTIN	4045197698742
Item class	32X

Description**Version:**

Precisely tempered, ground on the external and internal Ø, shank to DIN 1835 B. Concentricity 0.01 mm. **For side lock arbor with bore Ø (d₃) 20 or 25 mm.**

Application:

For holding slitting saws No. 175000 – 179820 with Ø (d₁) from 20 – 100 mm and saw blade thicknesses from 0.2 – 6 mm.

Supplied with:

Arbor, clamping screw and intermediate ring.

Technical description

Ø d ₃	20 mm
Ø d ₂	8 mm
A	50 mm
Ø d ₄	13 mm
Length L	100 mm
for saw blade Ø d ₁	25 mm
Type of product	Slitting saw arbor

Accessories

Spare screw for slitting saw arbor for saw blade Ø d1 25 mm

345566 25

Spare washer for slitting saw arbor for saw blade Ø d1 25 mm

345561 25