

**Vernier depth gauge, Measuring range: 500mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 418000 500    |
| GTIN         | 4045197203601 |
| Item class   | 41Z           |

**Description****Version:**

Measuring beam and vernier with clearly engraved scales. Precision ground contact faces.  
Vernier satin chrome-plated.

**Supplied with:**

From size 500 in a case.

**Technical description**

|                              |            |
|------------------------------|------------|
| Measuring range              | 0 - 500 mm |
| Bridge length                | 150 mm     |
| Measuring tip a              | 6 mm       |
| Vernier length               | 39 mm      |
| Graduation                   | 1/20 mm    |
| Cross-section measuring beam | 12×4 mm    |
| Measuring tip b              | 9 mm       |
| Packaging                    | sturdy box |
| Measurement deviation E MPE  | ± 0.1 mm   |
| Standard                     | ISO 13385  |
| Measurement technology       | analogue   |

|                 |                       |
|-----------------|-----------------------|
| Material        | Stainless steel, INOX |
| all parts       | hardened              |
| Calibration     | A1                    |
| Type of product | Depth gauge           |

### Services

|   |            |
|---|------------|
| CalibrationCalipers / depth gauges maximum measuring range 500 mm       | 021000 500 |
| DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm | 021010 500 |