

 Mahr**Digital caliper MarCal without measuring tips, Measuring range: 300mm****Order data**

Order number	415322 300
GTIN	4059192002916
Item class	43A

**Description****Version:**

**Direct reading from large and clear digital display. Precision lapped measuring faces.** The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032

**Optional extras:**

Data cable No. 498940.

**Technical description**

Measuring range	0 - 300 mm
Jaw length	90 mm
Calibration	A1
Internal jaw $\varnothing$	10 mm
Reversible reading	mm / inch
Scale divisions	0.0005 in
Scale divisions	0.01 mm

Error limit	0.03 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Works standard
Interface	USB interface
Interface	Digimatic interface
Interface	RS232 interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

## Accessories

Connection cablesimplex with data key Type D2	498940 D2
Connection cablesimplex with data key Type USB2	498940 USB2
Connection cablesimplex with data key Type R2	498940 R2
Button cell / special battery Battery type CR2032	081560 CR2032