



Digital workshop caliper, Measuring range: 500 mm



Order data

Order number	415528 500
GTIN	4045197492500
Item class	42A

Description

Version:

Easy-to-read display. Optimum guidance and sliding characteristics due to **double Vee guides**. Stainless steel jaws, precision ground. The left-hand measurement jaw is moveable.

Supplied with:

Manufacturer's test certificate. Up to size 1000 including plastic wallet, from size 1500 sturdy transport packaging.

1 battery No. 081560 size LR44.

Packaging: sturdy box

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.05 mm

Jaw length: 90 mm

Internal jaw \varnothing : 10 mm

Weight: 0.6 kg

Technical description

Jaw length	90 mm
Measuring range	0 - 500 mm
Calibration	A1
Internal jaw \varnothing	10 mm
Weight	0.6 kg
Scale divisions	0.01 mm

Error limit	0.05 mm
Article no of the battery / rechargeable battery fitted	081560 LR44
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 500 mm	011030 500
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 500 mm	011050 500
Calibration Calipers / depth gauges maximum measuring range 500 mm	021000 500
DAkkS calibration Calipers / depth gauges maximum measuring range 500 mm	021010 500

Accessories

Button cell / special battery Battery type LR44	081560 LR44
---	-------------