



Digital caliper MarCal without measuring tips, Measuring range: 750mm



Order data

Order number	415322 750
GTIN	4059192002954
Item class	43A

Description

Version:

Direct reading from large and clear digital display. Precision lapped measuring faces.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498940.

Reversible reading: mm / inch

IP Index of Protection: IP 65

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Error limit: 0.05 mm

Jaw length: 150 mm

Internal jaw \varnothing : 20 mm

Technical description

Jaw length	150 mm
Reversible reading	mm / inch
Internal jaw \varnothing	20 mm
Measuring range	0 - 750 mm

Calibration	A1
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Error limit	0.05 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	USB interface
Interface	Digimatic interface
Interface	RS232 interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 1000 mm	011030 1000
Labelling laser-etched Type	018940
DAkKS calibration Calipers / depth gauges maximum measuring range 1000 mm	011050 1000
DAkKS calibration Calipers / depth gauges maximum measuring range 1000 mm	021010 1000
Calibration Calipers / depth gauges maximum measuring range 1000 mm	021000 1000

Accessories

Connecting cable Type D2	498940 D2
Connecting cable Type R2	498940 R2
Connecting cable Type USB2	498940 USB2
Button cell / special battery Battery type CR2032	081560 CR2032