

Mitutoyo**Carbon digital caliper, Measuring range: 1000mm****Order data**

Order number	415400 1000
GTIN	4946368125275
Item class	44A

Description**Version:**

Measured result is displayed in easy-to-read digits.

With drive slide for constant measuring force. Extremely light. Selectable set-point (preset), selection of internal / external measurements (offset).

Function:

IP66: Protected against strong jets of water, and against temporary flooding and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497085.

Technical description

Calibration	A1
Weight	1.25 kg
Jaw length	150 mm
Internal jaw \varnothing	20 mm
Measuring range	0 - 1000 mm
Scale divisions	0.01 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1

Battery type	SR44
IP Index of Protection	IP 66
Power supply	Battery-powered
Measurement deviation E MPE	± 0.05 mm
Standard	ISO 13385
Interface	USB interface
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Packaging	sturdy box
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibration Calipers / depth gauges maximum measuring range 1000 mm	021010 1000

Accessories

Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type D1	497085 D1
Connecting cable with data switch Type D2	497085 D2
Connecting cable with data switch Type USB2	497085 USB2
Button cell / special battery Battery type 357	081560 357
Multi-receiver / USB keyboard interface Type	498975
Transmitter Type S11E	498966 S11E