

**Digital workshop caliper, Measuring range: 1000mm****Order data**

Order number	415530 1000
GTIN	4045197348524
Item class	42A

Description**Version:**

Easy-to-read display. Optimum guidance and sliding characteristics due to **double Vee guides**.

Stainless steel jaws, precision ground. The left-hand measurement jaw is moveable.

With Sylvac electronics.

Supplied with:

Manufacturer's test certificate. Up to size 1000 including plastic wallet, from size 1500 sturdy transport packaging.

1 battery No. 081560 size CR2032

Technical description

Calibration	A1
Measuring range	0 - 1000 mm
Jaw length	150 mm
Weight	1.7 kg
Internal jaw Ø	20 mm
Scale divisions	0.01 mm
Error limit	0.06 mm
#Article no of the battery / rechargeable battery fitted	081560 CR2032
#Number of batteries contained	1
Power supply	Battery-powered
Standard	Works standard

Packaging	sturdy box
Measurement technology	digital
all parts	hardened
Type of product	Workshop calipers

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/415530-1000>