



Slitting saw arbor, for saw blade \varnothing d1: 80mm



Order data

Order number	345510 80
GTIN	4045197698797
Item class	32X

Description

Version:

Precisely tempered, ground on the external and internal \varnothing , shank to DIN 1835 B. Concentricity 0.01 mm. **For side lock arbor with bore \varnothing (d₃) 20 or 25 mm.**

Application:

For holding slitting saws No. 175000 – 179820 with \varnothing (d₁) from 20 – 100 mm and saw blade thicknesses from 0.2 – 6 mm.

Supplied with:

Arbor, clamping screw and intermediate ring.

Technical description

Length L	150 mm
\varnothing d ₂	22 mm
\varnothing d ₄	34 mm
\varnothing d ₃	25 mm
A	92 mm
for saw blade \varnothing d ₁	80 mm
Type of product	Slitting saw arbor

Accessories

Spare screw for slitting saw arbor for saw blade \varnothing d1 80
mm

345566 80

Spare washer for slitting saw arbor for saw blade \varnothing d1 80
mm

345561 80