



Screw jack with magnetic base, highest support height: 62mm



Order data

Order number	373550 62
GTIN	4020772075804
Item class	35A

Description

Version:

Self-locking trapezoidal thread spindle with end stop.

The permanent magnet in the base of the screw jack ensures simple, lasting and precise positioning of the workpiece **on vertical faces**.

Note:

With centring hole \varnothing 12 mm for jack pads No. 375000 - 375010.

Technical description

Load capacity	30 kN
highest support height	62 mm
Lower part \varnothing	50 mm
Head \varnothing	50 mm
for clamp with slot width	14 - 22 mm
lowest support height	52 mm

Type	6400
Type of product	Screw jack