



Heavy screw jack, highest support height: 1250mm



Order data

Order number	374400 1250
GTIN	4020772072667
Item class	35A

Description

Version:

- Spindle quenched and tempered steel; body quenched and tempered steel, painted.
- Spindle with trapezoidal thread.

Note:

With centring hole \varnothing 12 mm for jack pads No. 375000 - 375030.

Technical description

highest support height	1250 mm
Centre slot spacing	150 mm
Head size AF	65 mm
lowest support height	710 mm
Slot width	26 mm
Load capacity	40 kN
Foot length	220 mm

Foot width	190 mm
Type	6435S
Type of product	Screw jack