



Hand-held belt file BF10-280E Starter set, Type: 72280551



Order data

Order number	077716 72280551
GTIN	4014586867267
Item class	03F

Description

Version:

High performance belt file with **comprehensive starter set**. Covers all important applications, with access to corners, edges, pipes, and profiles.

- **Very high metal removal rates in very small spaces.**
- **Optimal speeds for grinding belts, fleece belts and polishing belts, using adjustable speed range.**
- **Maximum reach 165 mm.**
- **Belt widths from 3 to 20 mm.**
- **Reliable belt guidance, even for the narrowest belts.**

Supplied with:

1 belt file BF 10-280 E in a plastic case, 3 grinding arms, 10 each grinding belts 3, 6, and 20 mm (120 grit) and 5 fleece belts 6 mm (medium grit).

Note:

Metal contact roller available on request.

Technical description

Power consumption	800 W
Weight	2.1 kg
Manufacturer's designation	BF 10-280E

Band length	520 mm
maximum vibration to EN	< 2.5 m/s ²
Packaging	Carrying case
Speed range	10000 - 28000 min ⁻¹
Power supply	Mains operated
Tape width	3 mm
Tape width	6 mm
Tape width	20 mm
Type of product	Linishing machine