



## Height setting screw jack, highest support height: 115mm



### Order data

Order number	374480 115
GTIN	4020772086510
Item class	35A

### Description

#### Version:

- For precision alignment using fine pitch thread M 30×1.5. The fixed slide pad prevents the component from rotating and moving during alignment.
- The parallel pins supplied are Ø 12×50 mm and Ø 12×80 mm; they can be inserted in the centring hole, increasing the overall height by 30 or 60 mm.
- If the centring jack pad No. 375030 is placed under the screw jack, a support height of up to approx. 1370 mm can be achieved in combination with other screw jacks.

#### Note:

Flat component support face with centring hole Ø 12 mm for jack pads No. 375000 – 375030.

### Technical description

Lower part Ø	50 mm
lowest support height	75 mm
highest support height	115 mm
Load capacity	30 kN

Head size AF	46 mm
Type	6415
Type of product	Screw jack